



GLPOLY XK-GN30 Thermal Gel

Non-Silicone Thermally Conductive Putty Gel

| Description | Key Features | Typical Applications |
|--|--|---|
| Syringes packaging, automated production, high temperature, non-corrosive metal, 100% thermal curing putty. XK-GN series is a high performance thermal gel, based on TPR, filled with a variety of high-performance ceramic powder. It has high thermal conductivity, low thermal resistance, good insulation and infinite compression characteristics. | Thermal conductivity 3.0W/m.K High compressibility Non-silicone Non-curing resistance Resists Pump-out | Consumer electronics Automotive Systems Telecommunication |

Material Properties

| | Unit | XK-GN30 | Method |
|---|-------------------|-------------------|------------|
| Color | | Blue | Visual |
| Flow Rate (30cc EFD cartridges 0.100"orifice 90psi) | g/min | 15-25 | |
| Specific Gravity | g/cm ³ | 3.0±0.1 | ASTM D792 |
| Volume Resistivity | Ωcm | >10 ¹³ | ASTM D257 |
| Thermal Conductivity | W/mk | 3.0 | ASTM D5470 |
| Breakdown Voltage | KV/mm | >10 | ASTM D149 |
| Dielectric Constant | 1 | 8 | ASTM D150 |
| Low Limit BLT Thickness | mm | 0.09 | ASTM D374 |
| Application Temperature | °C | -30~150 | ASTM G166 |
| Shelf life | month | 12 | |
| Siloxane Volatile s D4~D20 | % | 0 | GC-FID |
| Flammability | UL94 | V-0 | UL94 |

Operating Procedures & Recommendation:

1. Options& Tools: automatic dispensing machine or manual feeding gun.
2. Recommended operating pressure for automatic gel-dispensing machine is 90psi .
3. No need maturing time, Instant gel-dispensing Immediately available .
4. The total amount of gel-dispensing is related to the pressure and the diameter of the glue gun.
5. Storage conditions: it can be stored under normal temperature and humidity. It is recommended that customers use the shelf for the best time of 6 months, with a deadline of 12 months.

Packing:

3 Standard Packing Editions as Following:

1st Edition: 55ml each pc of syringe , 7 layers *12 pcs, total 84pcs , standard carton size 41.5*34*34cm

2nd Edition: 100ml each pc of syringe, 5layers *12pcs, total 60pcs , standard carton size 44*34.5 *25.5cm

3rd Edition : 300ml of each pc of syringe ,2layers*8pcs, total 16 pcs , standard carton size 48.8*36.5 *14cm

Learn More

For additional information or Material Safety Data Sheets on the complete line of GLPOLY thermal interface management solutions, please call our office

tel: 86-755-27579310, visit www.glpoly.com or send a message to kemmy@glpoly.com.

Benefit & Advantage:

- 1.Ultra-low thermal resistance of thermal conductive gel, to optimize the heat dissipation performance of the product.
- 2.Convenience of r&d and design, because thermal conductive gel is paste and permanent adhesive , so in product design, there is no special consideration of product size and tolerance restrictions, can be flexibly designed according to the optimal effect of the design.
- 3.Convenience of purchasing management, thermal conductive gel with syringe packaging, one model can realize the needs of a variety of parts, a variety of products, greatly simplified the procurement management and storage management.
- 4.The thermal conductive gel process is automatic, syringe packaging, automatic dispensing process can be used, greatly improved the operating efficiency, reduced the labor cost and time cost, Meanwhile,optimized the stability of the product.
5. The material itself contains no solvent (environmental protection), no need to cure (fast), is the most advanced thermal conductive material, suitable for robot automatic assembly line.

LIMITED WARRANTY INFORMATION – PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that our products are safe, effective, and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

GLPOLY 's sole warranty is that our products will meet the sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

GLPOLY SPECIFICALLY DISCLAIMS ANY OTHER EXPRESS OR IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY.

GLPOLY DISCLAIMS ANY LIABILITY FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES.

GLPOLY is a registered trademark of Goldlink Tongda Corporation.

©2008, Goldlink Tongda Corporation.. All rights reserved.



*Email: kemmy@glpoly.com Tel: 86-755-27579310 Fax: 86-755-27579350
For the most direct access to technical support visit: www.glpoly.com*